

Model ED 23 | Drying and heating chambers with natural convection

The strengths of a BINDER ED series drying chamber include routine drying and sterilization tasks up to +300 °C. Thanks to the natural convection, all thermal processes which use this drying chamber are highly efficient. The ED series ensures fast, uniform drying.

BENEFITS

- Uniform drying conditions thanks to APT.line[™] technology
- · Identical test conditions throughout the chamber interior independent of sample size and quantity
- · Outstanding thermal insulation saves operation costs



Model 23

IMPORTANT FEATURES

- Temperature range: +5°C above ambient temperature to +300 °C
- APT.line[™] preheating chamber technology
- Natural convection
- Adjustable exhaust air flap

- Controller with timer functions
- 2 chrome-plated racks
- Class 2 independent adjustable temperature safety device (DIN 12880) with visual alarm

ORDERING INFORMATION

Interior volume [L]	Power supply - unit fuse	Plug*	Version	Model version	ArtNo.
Model ED 23					
	230 V 1~ 50/60 Hz -10,0 A	CEE 7/7	Standard	ED023-230V	9010-0190
20	120 V 1~ 60 Hz -12,5 A	NEMA 5-20	Standard	ED023UL-120V	9010-0192

435 mm

495 mm

520 mm

Option model	Standard	with RS 422	Standard	with RS 422		
Performance Data Temperature						
Temnerature ranne	+5 °C above ambient temperature to 300 °C	+5 °C above ambient temperature to 300 °C	+5 °C above ambient temperature to 300 °C	+5 °C above ambient temperature to 300 °C		
Temperature uniformity at 150°C	2.8 ± K	2.8 ± K	2.8 ± K	2.8 ± K		
Temperature fluctuation at 150°C	0.5 ± K	0.5 ± K	0.5 ± K	0.5 ± K		
Heating up time to 150°C	28 min	28 min	28 min	28 min		
Recovery time after door was opened for 30 s at 150°C	5 min	5 min	5 min	5 min		
Air change data						
Air change rate at 150°C	13 x/h	13 x/h	13 x/h	13 x/h		
Electrical data						
Rated Voltage	230 V		120 V			
Power frequency	50/60 Hz	50/60 Hz	60 Hz	60 Hz		
Nominal power	0,8 kW	0,8 kW	0,8 kW	0,8 kW		
Unit fuse	10,0 A	10,0 A	12,5 A	12,5 A		
Phase (Nominal voltage)	1~	1~	1~	1~		
Dimensions and weights						
Interior volume	20 L	20 L	20 L	20 L		
Net weight of the unit (empty)	27 kg	27 kg	27 kg	27 kg		
Load per rack	12 kg	12 kg	12 kg	12 kg		
Permitted load	25 kg	25 kg	25 kg	25 kg		
Wall clearance back	100 mm	100 mm	100 mm	100 mm		
Wall clearance sidewise	50 mm	50 mm	50 mm	50 mm		
Housing dimensions not incl. fittings and connections						

435 mm

495 mm

520 mm

435 mm

495 mm

520 mm

ED023-230V-I

9010-0191

ED023UL-120V

9010-0192

Data

Width net


Height net

Depth net

Designation

Article Number

Data sheet Model ED 23



ED023-230V

9010-0190



ED023UL-120V-I

9010-0193

435 mm

495 mm

520 mm


Data sheet Model ED 23



Internal Dimensions				
Interior width	222 mm	222 mm	222 mm	222 mm
Interior height	330 mm	330 mm	330 mm	330 mm
Interior depth	300 mm	300 mm	300 mm	300 mm
Unit doors	1	1	1	1
Environment-specific data				
Energy consumption at 150°C	148 Wh/h	148 Wh/h	148 Wh/h	148 Wh/h
Fixtures				
Number of shelves (std./max.)	2/4	2/4	2/4	2/4

All technical data is specified for unloaded units with standard equipment at an ambient temperature of $+22 \text{ °C} \pm 3 \text{ °C}$ and a power supply voltage fluctuation of $\pm 10\%$. The temperature data is determined in accordance to BINDER factory standard following DIN 12880, observing the recommended wall clearances of 10 % of the height, width, and depth of the inner chamber. All indications are average values, typical for units produced in series. We reserve the right to change technical specifications at any time.

DIMENSIONS Incl. fittings and connections [mm]



OPTIONS

Designation	Description	ED 23	*	ArtNo.
	back			
	10 mm	•	01	8012-1282
	30 mm	٠	01	8012-0540
	50 mm	•	01	8012-0546
	left			
Access port with silicone plug	10 mm	•	01	8012-1275
	30 mm	•	01	8012-0537
	50 mm	•	01	8012-0542
	right			
	10 mm	•	01	8012-1268
	30 mm	•	01	8012-0536
	50 mm	•	01	8012-0541

Data sheet Model ED 23

BINDER Best conditions for your success

Designation	Description	ED 23	*	ArtNo.
	top			
	10 mm	•	01	8012-1262
	30 mm	•	01	8012-0539
	50 mm	•	01	8012-0545
	Switchable acoustic alarm, with adjustable limit value on the independent temperature safety device			
	120/208 V option model	•	-	8012-1303
Narm function for overheating	switchable acoustic alarm, with adjustable limit value on the independent temperature safety device. Not in combination with the following option: Door with window			
	230/400 V option model	•	-	8012-1299
Analog output 4-20 mA	for temperature values (output not adjustable)	•	-	8012-0430
Calibration certificate, expanded	for temperature; for extending the measurement in center of chamber to include another test temperature	•	-	8012-1115
Calibration certificate, temperature	for temperature, measurement in center of chamber at specified temperature	•	-	8012-1134
	temperature measurement incl. certificate, 9 measuring points at specified temperature	•	-	8012-1551
	temperature measurement incl. certificate, 15- 18 measuring points at specified temperature	•	-	8012-1572
	temperature measurement incl. certificate and 27 measuring points at specified temperature	•	-	8012-1593
Class 3.1 independent emperature safety device	with visual alarm (DIN 12880)	•	-	8012-0032
Door gasket	made of FKM, silicone-free	•	-	8012-0493
Door lock	lockable door handle	•	-	8012-1246
Measurement of air exchange rate	in accordance with ASTM D5374, definition and protocol according to ambient temperature	•	-	8012-0195
Pt 100 temperature sensor	additional flexible Pt 100, interior, with external connection incl. LEMO connector (3-pin)	•	-	8012-1173
Viewing window and interior lighting	Viewing window 180×180 mm in the door and interior lighting 15 W. Not in combination with the following option: Alarm function for overheating			
	230 V option model	•	-	8012-0378
CCESSORIES				
Designation	Description	ED 23	*	ArtNo.

pH-neutral detergent concentrated, for gentle remove of residual contaminants; 1 kg • - 8012-2250

Data sheet Model ED 23

BINDER Best conditions for your success

Designation	Description	ED 23	*	ArtNo.
	IQ/OQ/PQ documents – supporting documents for validation performed by customers, according to customer requirements, PQ section added to qualification folder IQ/OQ; parameters: temperature, CO ₂ , O ₂ – or pressure, depending on unit			
	- Digital in PDF format	•	-	7057-0005
	- Hard copy inside folder	•	-	7007-0005
Qualification documents	IQ/OQ documents – supporting documents for validation performed by customers, consisting of: IQ/OQ checklists incl. calibration guide and comprehensive unit documentation; parameters: temperature, CO ₂ , O ₂ , pressure, depending on unit			
	Digital in PDF format	•	-	7057-0001
	- Hard copy inside folder	•	-	7007-0001
Rack	chrome plated	•	-	8012-2031
	stainless steel	•	-	8012-2046
Rubber pads	set anti-slip feet	•	-	8012-2030

SERVICES

Designation	Description	*	ArtNo.
Calibration services			
Calibration and Franks, between the	Calibration of one (1) test temperature specified by the user in center of chamber, including certificate	-	DL30-0110
Calibration certificate, temperature	Extension of calibration of one (1) additional test temperature specified by the user in the center of the usable space, including certificate	_	DL30-0102
Measurement of air exchange rate	including certificate (in accordance with ASTM D5374)	_	DL33-0000
Temperature measurement, 9 measuring points	Temperature measurement with 9 measuring points with a set value specified by the user, including certificate	_	DL30-0109
Temperature measurement, 18 measuring point	$_{\rm S}$ Temperature measurement with 18 measuring points with a set value specified by the user, including certificate	_	DL30-0118
Temperature measurement, 27 measuring points	Temperature measurement with 27 measuring points with a set value specified by the user, including certificate	_	DL30-0127
Installation services			
Unit commissioning	Connect the unit to the customer-side connections (electricity, water, wastewater, gas), basic functions check, brief operating instructions. (excl.: unpacking, setup, controller instructions, programming, installation work)	-	DL10-0100
Unit instructions	Instruction regarding operating principle and basic functions of the unit, operation of the control electronics including programming	_	DL10-0500
Maintenance contracts			
BRONZE 3-year maintenance contract	Maintenance service as contractually agreed, visual inspection of mechanical and electrical components, check of control response, 20% discount on spare parts	_	DL20-0720
GOLD 3-year maintenance contract	Maintenance service as contractually agreed, visual inspection of mechanical and electrical components, check of control response, 20% discount on spare parts,	_	DL20-0915

BINDER Best conditions for your success

Designation	Description	*	ArtNo.
	testing of all key functions, replacement of wear parts, calibration of one test temperature specified by the user in the center of the usable space, including certificate		
SILVER 3-year maintenance contract	Maintenance service as contractually agreed, visual inspection of mechanical and electrical components, check of control response, 20% discount on spare parts, testing of all key functions, calibration of one test temperature specified by the user in the center of the usable space, without certificate	_	DL20-0815
Maintenance services			
Maintenance	One-off maintenance service in accordance with maintenance schedule. Visual inspection of mechanical and electrical components, testing of all key functions. Calibration of a test temperature specified by the user in center of usable space without certificate	-	DL20-0601
Validation services			
Execution of IQ/OQ	Execution of IQ/OQ in accordance with qualification folder	-	DL40-0100
Execution of IQ/OQ/PQ	Execution of IQ/OQ/PQ in accordance with qualification folder	_	DL44-0500
Warranty service			
1-year warranty extension	The warranty is extended by 1 year from the delivery date, wear parts are excluded	-	DL50-0010

NOTES

01 Condensation may occur in the area around the access port. Access ports may be placed in custom locations for an additional charge.

BINDER GmbH Tuttlingen, Germany TEL +49 7462 2005 0 info@binder-world.com www.binder-world.com

BINDER Asia Pacific (Hong Kong) Ltd. Kowloon, Hong Kong, P.R. China TEL +852 39070500 asia@binder-world.com www.binder-world.com BINDER Inc. Bohemia, NY, USA TEL +1 631 224 4340 usa@binder-world.com www.binder-world.us BINDER Environmental Testing Equipment (Shanghai) Co., Ltd. Shanghai, P.R. China TEL +86 21 685 808 25 china@binder-world.com www.binder-world.com