

Klik hier voor meer informatie op vonmarcken.nl

3 drawers and 1 shelf temperature memory Connection for forwarding Forced-air cooling alarms and for PC-supported temperature documentation Standalone or undercounter installation Antifreeze Visual and audible alarm signal, even in the case of power failure Key switch Digital temperature display Automatic defrosting Low-noise compressor




Condensate evaporation



#### Low-noise compressor

Reduces noise by 10 dB to 40 dB (corresponds to noise level I; sounds perception: whisper).



High temperature precision even when built in thanks to forced-air cooling and a highperformance, ventilated refrigerating machine.

Minimum/maximum

# MED-100



















#### according to DIN 58345

- **External housing** made from galvanised sheet steel (rustproof), with white, anti-scratch powder coating. Length of the plug cable: approx. 1.8 m.
- Adjustable feet positioned at the front to compensate uneven floors.
- Interior made from impact-resistant, white plastic with moulded-in shelves.
- Interior consists of three drawers with stops and a plasticcoated shelf. There is one adjustable length divider and six adjustable cross dividers per drawer. Storage surface per drawer =  $0.13 \text{ m}^2$ .
- Extra-thick 50-mm insulation, made from high-quality, compression-moulded and environmentally friendly material. Energy saving.
- Door with easy-to-replace plastic magnetic seal frame, lockable.
- **Door hinge** on the right-hand side (by default, see illustration), or the left-hand side, can be retrofitted.
- Forced-air cooling with axial blower, switches off automatically when you open the door, ensures a uniform temperature and minimizes temperature deviations.
- Automatic defrosting with time limit and temperature monitoring.

- Condensate evaporation in the refrigerating machine
- Key switch protected control panel against tampering. Membrane keyboard with digital temperature display and minimum/maximum temperature memory.
- Warning functions with visual and audible alarm signal in the case of temperature deviations and power failure. In the case of power failure, the monitoring unit remains in operation for approx. 72 hours on battery power. Door open alarm after 60 seconds.
- Alarms can be forwarded using the floating contact (e.g., to a mobile phone with optional GSM-Module or to a control centre).
- RS485 interface for connecting to PC-supported temperature documentation (using the optional KIRSCH-PC-KIT).
- Antifreeze against sub-zero temperatures
- Ventilation-enforced refrigerating machine, hermetically sealed, energy saving, low-noise, easy to service. Inlet air and exhaust air flow through the ventilation slits at the
- Low-noise compressor reduces noise by 10 dB to 40 dB (corresponds to noise level I; sound perception: whisper).

### Specification

| Capacity  | 95 litres   |
|---|---|
| Temperature setting                               | approx. +2 °C to +20 °C   |
| Voltage   | 220 – 240 V, 50/60 Hz   |
| Power consumption                                 | 160 watts   |
| Normal consumption                                | 0.65 kWh/24 h   |
| Admissible ambient temperature                    | from +10 °C to +38 °C   |
| Heat emission (max.)                              | 227 watts   |
| Overall dimensions (including distance from wall) | w x d x h = 54 x 53.5 x 82 cm   |
| Interior dimensions                               | w x d x h = 44 x 43 x 47 cm<br>(usable depth 5 cm, usable<br>width 2 cm less) |
| Exterior dimensions with door open at 90°         | w x d = 54 x 105.5 cm   |
| Shelf size  | 43.8 x 33 cm  |
| Drawer inner dimensions                           | w x d x h = 40.8 x 32 x 5.6 cm  |
| Max. load:<br>drawer/shelf                        | 13 kg/25 kg   |
| Weight  | Net weight 46 kg, gross weight 50 kg  |

## Optional equipment

- Glass door with lock.
- Tabletop (exterior dimensions: 85 cm in height).
- Decorative door frame for attaching the customer's decorative plates (exterior dimensions: 55 cm in width).
- Door fitting.
- Equipped with castors.
- Additional length and cross dividers.
- Shelf instead of drawer.
- Condensate container can be emptied manually if no condensation is required (e.g., in an operating theatre).
- GSM-Module for alarm text message transmission (e.g., to a mobile phone).
- Temperature documentation:
  - PC-KIT-NET, PC-KIT-USB-MONITORING or PC-KIT-STICK including software for temperature documentation.
  - 4-pin PT 100 or PT 1000 temperature sensor, class 1/3 B, including built-in reference body (measurement bottle or refrigerating block).
  - Mechanical pen-recording thermometer with two waxed paper strips.